



History & Innovation

At the end of 2005, a professional range of high quality loudspeakers was born – LOTUSLINE.

to SIC [™] technology in Lotusline SB series 2007 MVC [™] technology in Lotusline MA series 2009 LOTUSLINE acquired its own compiler software EASE Focus, called LA system. 2011 LOTUSLINE applied a new proprietary technology CLS [™] (Coax line source) technology. 2013 LOTUSLINE has licensed EASE Focus 2 and applied a new proprietary technology, SSA [™] (Spherical source array) 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series.	2006	LOTUSLINE has applied three proprietary technologies in three series:			
 2007 MVC[™] technology in Lotusline MA series SHM[™] collinear waveguide technology in Lotusline LA system 2009 LOTUSLINE acquired its own compiler software EASE Focus, called LA system. 2011 LOTUSLINE applied a new proprietary technology CLS[™] (Coax line source) technology. 2013 LOTUSLINE has licensed EASE Focus 2 and applied a new proprietary technology, SSA[™] (Spherical source array) 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. 2021 LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio 	to				
2007 SHM™ collinear waveguide technology in Lotusline LA system 2009 LOTUSLINE acquired its own compiler software EASE Focus, called LA system. 2011 LOTUSLINE applied a new proprietary technology CLS™ (Coax line source) technology. 2013 LOTUSLINE has licensed EASE Focus 2 and applied a new proprietary technology, SSA™ (Spherical source array) 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. 2021 LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio					
2009 called LA system. 2011 LOTUSLINE applied a new proprietary technology CLS [™] (Coax line source) technology. 2013 LOTUSLINE has licensed EASE Focus 2 and applied a new proprietary technology, SSA [™] (Spherical source array) 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. 2021 LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio	2007				
2011 line source) technology. LOTUSLINE has licensed EASE Focus 2 and applied a new proprietary technology, SSA™ (Spherical source array) 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. 2021 LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio	2009				
2013 proprietary technology, SSA™ (Spherical source array) 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. 2021 LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio	2011	LOTUSLINE applied a new proprietary technology CLS [™] (Coaxia line source) technology.			
 2013 SSA based cabinets are arrayable asymmetrical elements to be used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. 2021 LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio 		LOTUSLINE has licensed EASE Focus 2 and applied a new			
used unitary or coupled up to full hemispherical perfectly coher point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio					
point source. 2016 LOTUSLINE first proposed the concept of spherical waves. Th technology was first applied to the SSA series. LOTUSLINE officially authorized the establishment of the Asia 2021 Pacific Operations Center in Guangzhou, China. This operatio	2013	SSA based cabinets are arrayable asymmetrical elements to be			
2016 technology was first applied to the SSA series. LOTUSLINE officially authorized the establishment of the Asia 2021 Pacific Operations Center in Guangzhou, China. This operatio		used unitary or coupled up to full hemispherical perfectly coheren point source.			
LOTUSLINE officially authorized the establishment of the Asia Pacific Operations Center in Guangzhou, China. This operatio	2010	LOTUSLINE first proposed the concept of spherical waves. This			
2021 Pacific Operations Center in Guangzhou, China. This operatio	2016	technology was first applied to the SSA series.			
		LOTUSLINE officially authorized the establishment of the Asia-			
center works closely with Europe to become a big family.	2021	Pacific Operations Center in Guangzhou, China. This operations			
		center works closely with Europe to become a big family.			
LOTUSLINE first proposed the concept of precise adjustable		LOTUSLINE first proposed the concept of precise adjustable			
2024 radiation and adaptive adjustment , to fully prepare for the	2024	radiation and adaptive adjustment, to fully prepare for the			
innovative application of AI in the field of professional acoustic		innovative application of AI in the field of professional acoustics			
in the future		in the future			

LOTUSLINE systems are state of the art innovative products and offer the sound designer, sophisticated but easy to use electro acoustic tools, which are the key to sound.

Contact & Support

EUROPE

LOTUSLINE ACOUSTICS SARL FRANCE 26 rue Damrémont 75018 Paris FRANCE E-mail: info-fr@lotuslinepro.com Web: www.lotuslinepro.com CHINA LOTUSLINE ELECTRO ACOUSTICS CO. CHINA

#101 No.178 Jinlong Road Shiqi Town Panyu District Guangzhou CHINA E-mail: info-ch@lotuslinepro.com Web: www.lotuslinepro.com

Forget the system and enjoy the sound !

Technologies



The key to Sound

Coaxial Technology

Classical arrangement of two way loudspeakers uses separate transducers positioned on a common front baffle. In the transition frequency region, due to the difference of path length between the listening point and the two separate sources, spatial frequency answer cannot be homogenous. This problem is particularly sensitive for short field listening such as stage monitoring and small venues.

By superposing both of the two sources, coaxial technology eliminates the problem and creates a perfect homogenous acoustic field on all the speaker coverage as well horizontally as vertically.

The advantages of the coaxial approach include: single point source radiation, total wavefront coherency at all frequencies and superimposed LF/HF dispersion characteristics that are free of polar lobbing effects typical of traditional horn and woofer combinations. The net result is natural, studio monitor level sound quality that is ideal for proximity use.

Lotusline MA & MQ series include two different coaxial arrangements.

The first one uses the main driver cone as horn load for the HF driver.

This arrangement offer the largest possible conical coherent coverage and is used in MA8v₂, MA10v₂, MA12v₂ and MA15v₂.

The second one uses a separate horn for the HF driver.

This arrangement offers smaller aperture angles and higher lomid efficiency by loading the main cone in its throat region. We call it "active" horn loading.

This arrangement is used in MQ60.

Line Source Technology

All line arrays are not line sources ! What's the difference ?


A true line source array generate an homogenous acoustic field on all its coverage area, in all its frequency range and is free of interference problems. The net result is the same sound from near field to far field.

The conception of a true line source encounters a lot of technical problems the designer has to solve. The main one is the fusion of all individual sources in only one virtual line source in order to generate on all the frequency range a perfect free of lobbing effects toroidal wavefront. If the solution is evident for low frequencies, this is not the same piece of cake for high ones. The acoustical size of a sound source is close to the wavelength of the generated signal. At 100Hz, the wavelength is 3.4m, so, two speakers distant of 1.2m (half the wavelength) create a perfect coherent source. At 1kHz, the wavelength is only 34cm and these two speakers are no more a coherent source and generate interferences. At 10kHz, the wavelength is 3.4cm and there are no speakers able to realize the performance to be smaller than 1.7cm in the real professional sound reinforcement world.


Many improvements have been made in line source technology, but the physical remain the same.

SHM[™] and SIC[™], Lotusline proprietary technologies applied in LA series, are fundamental improvements in professional loudspeaker design.

By respecting line source rules and all other acoustic laws, Lotusline LA series are true line source line arrays with a real behaviour close to the mathematical theory.



Standard coaxial arrangement



Coaxial active norn arrangement

Proprietary Technologies

SHM[™] Technology

SHMTM (Single Horn loaded Midrange) improve dramatically midrange bandwidth and efficiency by avoiding multiple components dispersion and using collinear mid and hi frequency horns layout.

First line array uses mid drivers on plane baffle. Small improvements in efficiency have been made by using compression load midrange directly in the front common waveguide, but creating irregularities in frequency response, and dispersion in characteristics due to the multiplication of components. Actually, coaxial midrange equipped with rear standard HF driver is used in common acoustic chamber imposing a long path to high frequency waves. Lotus Line Array uses the shortest possible design by positioning the toroidal HF drivers in front of the midrange driver.

SHM[™] technology reduces the total harmonic distortion both in high frequencies by minimizing the length of waveguides and in low mid by increasing the radiating surface of the driver.

CLS[™] Technology

CLS™ (Coaxial Line Source)technology is the definitive solution for two way configuration line source symmetrical array systems.

Standard two way line source arrays using only one low frequency driver are asymmetrical cabinets, CLS[™] based Lotusline CL series are symmetrical and optimized minimum front baffle sized.

CLSTM technology offers all advantages of coaxial active horn arrangement applied to line source array systems. It means, minimum front baffle size, perfect symmetry of the baffle and so, perfect symmetry of the coverage.

Lotusline CL series uses **CLS**TM technology, increasing the efficiency in low mid region, shaping the wavefront from spherical to ovoid and increasing consequently the maximum crossover frequency in vertical coupling.

SSA[™] Technology

SSA™ (Spherical Source Array) technology is Lotusline's answer to an old question: How to build a high SPL, compact and configurable, true point source system?

SSA[™] cabinets are mathematically equivalent to a portion of a spherical segment whose acoustic centre at the centre of the mother sphere. In more simple words, SSA[™] cabinets are like pieces of orange, they can be used individually and can also rebuild a complete fruit. SSA[™] cabinets are perfectly arrayable without audible interferences, even in very high frequencies.

Each cabinet can be used unitary for covering small areas or coupled with other SSATM cabinets for larger ones.

MVC[™] Technology

MVCTM (Multi Vent Convection) technology, increase the power handling capacity of vented loudspeaker by combining acoustical and cooling functions of vents. Multiple curved vents are placed around the main loudspeaker offering a natural air convection flow lowering the temperature of the voice coil in any working position. **MVC**TM equipped speakers are much more thermal breakdown proofed than standard ones, and decrease thermal compression by lowering nominal temperature of the moving coil.

The MVC[™] (multi vent convection) technology, allows the Lotusline CL, MQ and MA series to handle nominal full power capacity in any working position.

SIC[™] Technology

SIC[™] (Single Interactive Chamber) technology, increases bandwidth and efficiency while reducing total volume of vented bass loudspeaker by combining rear and front load in the same volume. Because rear and front load do not work in the same frequency region, it is possible, with a special calculation layout, to fuse both functions in only one. In practice, SIC[™] technology, by using this new physical approach, virtually suppresses one of the two volumes and dramatically reduce the total size of vent loaded subwoofer.

Further advantage of SIC[™] technology is the better cooling of the loudspeakers due to the exceptionally large size of the vent aperture.

Lotusline Technologies

SIC[™]technology used in SB Series

Best versus frequency-extension to size ratio Hi efficiency Better cooling

MVC[™] and Coaxial technologies used in MQ and MA Series Point source, regular spatial response, perfect acoustic field Better cooling, lo thermal compression in any working position

CLS[™], MVC[™] and Coaxial technologies used in CL Series True line source system Point source regular spatial response, perfect acousting

Point source, regular spatial response, perfect acoustic field Better cooling, lo thermal compression in any working position SSA[™], MVC[™] technologies used in SSA Series Spherical source array system Point source arrangement Better cooling, lo thermal compression in any working position

SHM[™]and line source technologies used in LA Series True line source system Low distortion at hi SPL Perfectly coherent arrays controlling vertical opening







The key to Sound

SSA[™], MVC[™] techno

Point Source system



MA series

MA 15v₂ / MA 12v₂ / MA 10v₂ / MA 8v₂

The Lotusline MA series loudspeaker enclosures provide a versatile system that is designed for high quality distributed sound reinforcement or high performance monitoring. Using true point source coaxial technology, the Lotusline MA series features advanced components in a flexible, multipurpose format that is suitable for either touring or fixed installation.

The MA series are passive two-way loudspeaker. The low/mid section comprises a bass driver loaded in a 4thorder MVC[™] enclosure, The hi section includes a High Frequency compression driver assembled in a coaxial configuration along with the full low section loudspeaker providing a conical opening.

Further advantages of the coaxial approach include: single point source radiation, total wavefront coherency at all frequencies and superimposed LF/HF dispersion characteristics that are free of polar lobbing effects typical of traditional horn and woofer combinations. The net result is natural, studio monitor level sound quality that is ideal for proximity use.

The MA series provides a very coherent acoustic field with 90°-120° conical coverage.

The MVC[™](Multi Vent Convection) technology, allows the Lotusline MA series to handle nominal full power capacity in any working position.

The enclosure comprises two angles side, 45° and 60° for stage monitor application and include two 35mm built in stand supports as well as four wood integrated handles and 5 cargo standard rigging points.

The Lotusline MA series crossovers are build with air core inductors, MKP capacitors and wirewound resistors.

The Lotusline MA series apply full power handling with low thermal compression.

Product line / Fly rigging accessories



MA Series



- 415

60

Тор



The Lotusline MA15v2 loudspeaker enclosures provide a versatile system that is designed for high quality distributed sound reinforcement or high performance monitoring. Using true point source coaxial technology, the Lotusline MA series features advanced components in a flexible, multipurpose format that is suitable for either touring or fixed installation.

The MA15v2 is a passive two-way loudspeaker. The low/mid section comprises a 15 inch bass driver loaded in a 4th order MVC[™] enclosure, The hi section includes a 1.4 inch high frequency compression driver assembled in a coaxial configuration along with the full low section loudspeaker providing a conical opening.

The MA15v2 provides a very coherent acoustic field with 90° conical coverage.

As a main F.O.H the MA15v2 is meant for vocal applications, stage monitoring or distributed sound. Combined with Lotusline subwoofers, the MA15v2 allows to create compact and powerful systems suitable for all indoor or outdoor configuration.

The MA15v2 is also ideal for distributed sound reinforcement and can be used in medium power front-of-house (FOH) applications for theatres, clubs, multi-purpose venues or corporate events.

Specifications

opeennearierie				
FEATURES	Low Section	High Section		
Frequency range with processor (±3dB)	55Hz to 1100 Hz	1100 Hz to 20 kHz	680	
Sensitivity@1W/1m, f>80Hz1	100	dB SPL		
Maximum continuous level at 1m ²	127 dB SPL			
Peak level at 1m, f>65Hz	133			
Nominal impedance	8	Front		
Nominal horizontal coverage@-6dB ³	90°			
COMPONENTS			397	
Transducers	1 x 15" weatherproof loudspeaker	1 x 1.4" throat compression driver coaxially mounted		
Coil diameter	75 mm	45 mm		
Type of load	MVC [™] Bass reflex	Conical Horn	I	
Power (AES/ Peak)	500 V			
CONSTRUCTION & CHARACTERISTICS				
Cabinet	18mm birch plywood with inter			
Crossover	Internal passive network	Side		
Connectors ⁴	4 x Speakon NL4MP			
Handles	4 wood integrated handles			
Rigging	4 inserts for Omnimount 60 ser			
Dimensions (H x W x D)	680 x 452 x 397 mm 412			
Net unit weight	31.5 kg 69.4 lbs			
Gross weight, packed	34.6 kg 76.3 lbs			

. Sensitivity is the average SPL measured over the components rated bandwidth

Power rating displays the long term AES power handling capacity using pink noise with a 6 dB crest factor over the components rated bandwidth
 Directivity is averaged over the 600Hz-12 kHz range.
 The SPEAKON connectors are wired, hot : pin 2+, cold : pin 2-.



LOTUSLINE ACOUSTICS SAR FRANCE

26 rue Damrémont 75018 Paris, FRANCE E-mail: info@lotuslinepro.com • Web: www.lotuslinepro.com